

INSTALLATION INSTRUCTION

REMOTE TRIGGER KIT – USE WITH P4 SERIES AND THE LS2000 / LS3000 DISPENSING SYSTEMS

The Remote Trigger Kit (Item #087132) includes:

- Trigger with 15 feet power cord
- Plug-in 120V transformer with 12” power cord.

Place switch in accessible location. The switch must be within 12 feet of power outlet and 15 feet of pump. Install wiring as described:


For Individual Pump Triggering (P4 Series):

1. Connect the red wire from the plug-in transformer to the positive (+) trigger terminal on the Multi-time module.
2. The black wire from the transformer should enter the pump enclosure and be capped together with the black wire from the remote trigger switch.
3. The red wire from the remote trigger switch should be connected to the negative trigger terminal on the Multi-time Module.
4. To activate pump, depress trigger until pump activates.


For Multiple Pump Triggering (LS2000/LS3000):

1. Connect the red wire from the plug-in transformer to the positive (+) trigger terminal on the first Multi-time module in the series to be triggered simultaneously.
2. The black wire from the transformer should enter the pump enclosure and be capped together with the black wire from the remote trigger switch.
3. The red wire from the remote trigger switch should be connected to the negative trigger terminal on the first Multi-time module in the series.
4. Wire each additional Multi-time module in parallel (i.e. connect positive (+) trigger terminal to positive (+) trigger terminal and negative (-) trigger terminal to (-) trigger terminal)

To activate the pump series, depress the trigger until pumps activate.



Remote Trigger Kit for Individual Pump Triggering



Remote Trigger Kit for Multiple Pump Triggering

Beta
Beta Technology, Inc
2841 Mission Street
Santa Cruz • CA
U.S.A. • 95060
TEL • 831 • 426 • 0882
TEL • 800 • 958 • 2382
FAX • 831 • 423 • 4573
FAX • 800 • 221 • 8116
TEL • 800 • 215 • 6415 • Tech Support
sales@beta-technology.com

Beta Technology, Inc
4 Finway, Dallow Road
Luton LU1 1TR
United Kingdom
Freephone • 0800 • 052 • 4726
Tel • +44(0) • 1582 • 528600
Fax • +44(0) • 1582 • 528111
Freephone • 0800 • 052 • 4726
VAT REG NO: BG-354-09975-44
europe.sales@beta-technology.com
Customer Service
Tech Service
Online Ordering: <http://www.beta-technology.com>